

Magnetic Stirring Rods, BÜRKLE

fish-clip®

Gentle magnetic stirring - also in vessels with small openings.

After the magnetic stirring bar is attached to the elastic clip of the rotor, it can be fixed at a variable height above the vessel base. If the rotor then is driven by the magnetic stirrer, it rotates in a controlled manner, protecting the stirred substance and the vessel. The holding rod is not rotating, the closure keeps gastight for a long time.

- Holding rod and rotor made of PVDF
- Thermally resistant up to 160 °C, sterilizable
- For magnetic stirring bars with diameters of 6 mm or 8 mm
- Holding rod length 25 mm
- Compression-type bung in silicone for NS 19/26 and NS 29/32
- Compression-type fittings GL 25, GL 32
- Adapter for NS 19/26 and 29/32
- Also suitable for viscous media

Article	Magnetic stirring bars Ø mm	Order No.
fish-clip® gas-tight, PVDF blue, incl. stirring bars	6	51 05 80006
fish-clip® gas-tight, PVDF red, incl. stirring bars	8	51 05 80008

Accessories

Article	Color	Order No.
Clamping stopper made of silicone for NS 19/26		51 05 80127
Clamping stopper made of silicone for NS 29/32		51 05 80632
Clamping coupling GL 25	red	51 05 80025
Clamping coupling GL 32	gray	51 05 80032
Clamping coupling GL 25 with NS adapter for NS 19/26	red	51 05 80125
Clamping coupling GL 32 with NS adapter for NS 29/32	gray	51 05 80132

Magnetic stirring bars, round, PTFE white

Ø mm	Length mm	Order No.	Ø mm	Length mm	Order No.
6	10	51 05 71006	6	30	51 05 73006
6	15	51 05 71506	8	40	51 05 74008
6	20	51 05 72006	8	50	51 05 75008
6	25	51 05 72506			

