

## Eye Wash Bottles, EKASTU

EKASTU eye wash bottles are used in first aid to rinse out the eyes and remove any foreign particles before therapeutic treatment begins. It is recommended that an EKASTU eye wash bottle is always kept ready and within reach whenever carrying out painting or work involving dirt, chemicals and dust. In sealed condition for very long duty.

### EKASTU eye wash bottles

| Article                                                                                                                                                                                                                               | Order No.          |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| ① <b>Eye wash bottle w. funnel a. tilting valve, empty (600 ml)</b>                                                                                                                                                                   | <b>36 52 20001</b> |
| For immediate rinsing of the eyes after contact with acids, alkalis, etc. PE bottle with screw-fitted eye funnel and tilt valve. Spill-proof. The tilt valve allows you to rinse out the eyes in either a standing or lying position. |                    |

| Article                                                                      | Order No.          |
|------------------------------------------------------------------------------|--------------------|
| <b>Eye wash bottle with funnel and tilting valve, full (600 ml)</b>          | <b>36 52 77959</b> |
| Same as the EKASTU eye rinse bottle, empty (600 ml), but with water filling. |                    |

| Article                                                                             | Order No.          |
|-------------------------------------------------------------------------------------|--------------------|
| <b>Eye wash bottle ECO with funnel, full (600 ml)</b>                               | <b>10 52 37111</b> |
| As previous EKASTU-eye wash bottle, but in economic version, without tilting valve. |                    |

| Article                                                                                                                                                                                                                                                                                                           | Order No.          |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| <b>Eye wash bottle mini with funnel a. tilting valve, empty (175 ml)</b>                                                                                                                                                                                                                                          | <b>36 52 77251</b> |
| For immediate rinsing of the eyes after contact with acids, alkalis, etc. PE bottle with screw-fitted eye funnel and tilt valve. Spill-proof. The tilt valve allows you to rinse out the eyes in either a standing or lying position. Ergonomic shape for carrying comfortably in a breast pocket or coat pocket. |                    |

| Article                                                                           | Order No.          |
|-----------------------------------------------------------------------------------|--------------------|
| <b>Eye wash bottle mini with funnel a. tilting valve, full (175 ml)</b>           | <b>36 52 77259</b> |
| Same as the EKASTU mini eye rinse bottle, empty (175 ml), but with water filling. |                    |

| Article                                                                             | Order No.          |
|-------------------------------------------------------------------------------------|--------------------|
| <b>Eye wash bottle ECO-mini with funnel, full (175 ml)</b>                          | <b>10 52 37112</b> |
| As previous EKASTU-eye wash bottle, but in economic version, without tilting valve. |                    |

| Article                                                                                                                                                                                                                                                                                                                                                                                                                   | Order No.          |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------|
| ② <b>Eye wash bottle ADR200, full (200 ml)</b>                                                                                                                                                                                                                                                                                                                                                                            | <b>10 52 37312</b> |
| Extremely sturdy. For applying a rinsing fluid into the eye socket and on the eye, filled with water, volume 200 ml. Curved PE bottle shaped from circular ring segments, with quick release screwed lid secured with a safety knurl. With unique, cylindrical pearl spray head stopper. With five integrated water channels parallel to the longitudinal axis of the stopper. Works in horizontal and vertical position. |                    |

### Accessories

| Article                                                                                  | Order No.          |
|------------------------------------------------------------------------------------------|--------------------|
| ③ <b>Eye wash station (EPS), empty</b><br>for 2 EKASTU eye wash bottles                  | <b>10 52 37955</b> |
| ③ <b>Eye wash station (EPS), complete</b><br>with 2 EKASTU eye wash bottles 175 + 600 ml | <b>10 52 37999</b> |
| ④ <b>Wall box with transparent lid for 1 eye wash bottle</b>                             | <b>36 52 20120</b> |
| ⑤ <b>Wall holder for 1 eye wash bottle</b><br>made of high quality coated steel wire     | <b>10 52 37950</b> |

