

Tamper-Evident Screw Cap, DURAN Group / IDL



Tamper-Evident Closure made of PP for DURAN® laboratory glass bottles

The tamper-evident closure, made of PP, can be used with all DURAN® labglass bottles with thread GL 45. It is used for safety storing the bottle contents. The cap is screwed tightly to the bottle and after a soft „click“ the plastic ring is fixed on the bottle neck. When the cap is opened for the first time, the perforation of the plastic ring is broken thus showing that the bottle has been opened.

The cap is autoclavable and temperature resistant up to +140°C.

After the perforation of the plastic ring is broken, the cap may of course still be used as an „ordinary“ screw cap.

Colour	Thread GL	Ø mm	Height mm	Order No.	PU pc/Pack
blue/red ¹⁾	45	54	26	11 29 17526	10
blue/yellow ²⁾	45	54	26	10 21 15886	10

❗ Available only in original packaging units. No fractions possible.

1) With lip seal

2) With PTFE protected seal

