

Volumetric flasks, PMP, transparent, BRAND

With PP stopper. Error limits (EL) according to class A, DIN EN ISO 1042. Class A incl. one batch certificate. Calibrated to contain (TC, In). Exposure to temperatures up to 121°C (autoclaving) will not cause permanently exceeded error limits! Cleaning up to max. 60°C is recommended to preserve marks and inscriptions. Pack of 1.

Volume ml	Error limit ± ml	Ground joint NS	Height mm	Order No.
10 W	0.04	10/19	90	10 49 36170
25	0.04	10/19	108	10 49 36172
50	0.06	12/21	146	10 49 36174
100	0.10	14/23	173	10 49 36176
250	0.15	19/26	225	10 49 36178
500	0.25	19/26	258	10 49 36180
1000	0.4	24/29	298	10 49 36182

W = wide neck, , height = without stopper

