

Flocculators, LAT

Flocculation tests have been developed for a series of applications, such as testing the efficiency of flocculation or precipitation agents. The portable unit is intended for mobile operation with battery or 12 V power supply. The units of the JLT and FC series offer reproducible results for four or six parallel samples over a wide speed range.

① Portable flocculator FP4

Technical data:

No. of stirring places: 4
 Speed: 20-40-50-100-200 rpm
 Lighting: central
 Dimensions: 250 × 320 × 250 mm
 Weight: 4.8 kg
 Power consumption: 6 W

Article	Order No.
Portable flocculator FP4	10 20 16004

Flocculators JLT series

Technical data:	JLT 4	JLT 6
No. of stirring places:	4	6
Speed:	10-300 rpm	10-300 rpm
Timer:	0-999 min/0-99 h	0-999 min/0-99 h
Lighting:	background	background
Dimensions:	645 × 347 × 260 mm	935 × 347 × 260 mm
Weight:	13 kg	17 kg
Power consumption:	11 W	19 W

Article	Order No.
Flocculator JLT4	10 20 16104
Flocculator JLT6	10 20 16106

② Flocculators with independent positions – FCS series

Technical data:	FC4S	FC6S
No. of stirring places:	4 independent positions	6 independent positions
Speed:	10-15-30-45-60-90-120-150-200 rpm	10-15-30-45-60-90-120-150-200 rpm
Timer:	continuously	continuously
Lighting:	background	background
Dimensions:	645 × 347 × 260 mm	935 × 347 × 260 mm
Weight:	12.5 kg	18 kg
Power consumption:	18 W	23 W

Article	Order No.
Flocculator FC4S	10 20 16204
Flocculator FC6S	10 20 16206



①



WWW4U080



②

